



TradeSelect, Straight Blade, Decorator Duplex Receptacle, Less Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

By Bryant
Catalog # [RRD15KGY](#)

TradeSelect, Straight Blade, Decorator Duplex Receptacle, Less Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray



Features

- Duplex
- Less Ears
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Residential Receptacles

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Push and Side Wire
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778100680
Color	Gray

Logistics

Carton Quantity	100
-----------------	-----