

## TradeSelect, Straight Blade, Decorator Duplex Receptacle, Less Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [RRD15KI](#)



TradeSelect, Straight Blade, Decorator Duplex Receptacle, Less Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

### Features

- Duplex
- Less Ears
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

### Application

Residential Receptacles

### General

Catalog Number	RRD15KI
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778100666

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Push and Side Wire
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

### Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

### Certifications And Compliance

Nema Rating	5-15R
-------------	-------

### Logistics

Carton Quantity	100
-----------------	-----

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - RRD15KI AutoCAD Drawing](#)  
[Sales Drawings - WDK\\_RRD15KI\\_DRAWINGS\\_PDF](#)  
[Specifications - RRD15KI Specification Sheet English](#)  
[Specifications - RRD15KI Specification Sheet French](#)