

## TradeSelect, Straight Blade, DecoratorDuplex Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

By Hubbell Wiring Device-Kellems  
Catalog # [RRD15S](#)



TradeSelect, Straight Blade, DecoratorDuplex Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

### Features

- DecoratorDuplex Receptacle
- Self Grounding
- 15A 125V

### Application

Residential Receptacles

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A

Voltage Rating Description	125 VAC
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Push and Side Wire
Wattage	1875
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Brown
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778100154

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)