

TradeSelect, Straight Blade, Decorator Duplex Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Brown

By Hubbell Wiring Device-Kellems
Catalog # [RRD15SLA](#)



TradeSelect, Straight Blade, Decorator Duplex Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Brown

Features

- Decorator Duplex Receptacle
- Self Grounding
- 15A 125V

Application

Residential Receptacles

Specifications

| | |
|--------------------------|---|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator | Yes |
| Nema Rating | 5-15R |

Conductor

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire Grounding |
| Wire Size | #14 AWG to #12 AWG |
| Number Of Poles | 2-Pole |

Current

| | |
|-----------------|------|
| Current Rating | 15 A |
| Amperage Rating | 15 A |

| | |
|----------------------------|--------------------|
| Voltage Rating Description | 125 VAC |
| Phase | Single Phase |
| Current / Amperage Rating | 15 A |
| Connectivity | Push and Side Wire |
| Wattage | 1875 |
| Voltage Rating | 125 VAC |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

General

| | |
|------------------------------|-------------------------------|
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Color | Light Almond |
| Item Type | Decorator Duplex |
| Material - Mounting Hardware | Screw Mounting |
| Material | Thermoplastic |
| UPC | 883778119293 |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)