

TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Duplex, Self Grounding, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [RRD15SW](#)

tradeSELECT® Straight Blade Decorator Duplex Receptacle, Self
Grounding 15A



Features

- Residential Grade
- Receptacles
- Decorator Duplex

Application

Residential Receptacles

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A

Voltage Rating Description	125 VAC
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Push and Side Wire
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778100178

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)