

TradeSelect, Straight Blade Residential Grade Receptacles, Weather and Tamper Resistant Decorator Duplex, Self Grounding, 15A 125V, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [RRD15SWWRTR](#)



TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Weather and Tamper Resistant Decorator Duplex, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

Features

- Weather and Tamper Resistant Decorator Duplex
- Self Grounding
- 15A 125V

Application

Residential Receptacles

Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A

Voltage Rating Description	125 VAC
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Push and Side Wire
Wattage	1875
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Color	White
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778303128

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

[Catalog \[English\]](#)