

Switches, Single Pole

15A, 120V AC

Residential Toggle Switch

HUBBELL

Features

- Hi-visibility yellow base for easy installation
- Elongated strap for easier wall box mounting
- Tough thermoplastic with ultrasonically welded cover and base

Ordering Information

Description	Color	UPC Number	Catalog Number
Toggle, Self-Grounding, Push & Side Wired	Light Almond	883778119347	RS115SLA

Listings

UL Listed E3896
CSA Certified



Specifications

Top Material	PVC
Base Material	PVC
Toggle Material	Nylon
Contacts	Silver Alloy
Terminal Screws	Brass
Auto Grounding Mounting Bridge	Galvanized Steel
Ground Screw	Steel (Green)
Mounting Screw	Zinc-Plated Steel

Performance

Electrical

Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	15A
Max. Working Voltage	120V AC
Overload	Minimum 1.5 times rating
Temperature Rise	30°C maximum at rated current

Mechanical

Terminal Accommodations	#14 AWG min. - #12 AWG max. solid and stranded copper wire only
-------------------------	---

Environmental

Flammability	UL 94 V-2
Operating Temperature	Maximum continuous 60°C; minimum -20°C (w/o impact)

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

