

TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [RT100W](#)



TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White

Features

- Cube Tap
- 15A 125V AC
- 2- Pole 3-Wire Grounding
- 5-15R

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	C/US UL Listed

Current

Current Rating	15 A
Amperage Rating	15 A
Current / Amperage Rating	15 A
Wattage	1875
Voltage Rating	125 VAC

General

Series

OEM Brand Name
Color
Item Type
Insulation
Material
UPC

Taps & Adaptors

Hubbell Wiring Device-Kellems
White
Adapters
Insulated Body
Composite
883778112461

Logistics

Carton Quantity 10

Operational

Operating Temperature
Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)