

# HUBBELL Premise Wiring

## SystemOne, Fire-Rated Poke-Through, 4" Fitting Only, (1) 3/4" EMT for Power, (2) 3/4" EMTs for Low Voltage

By Hubbell Premise Wiring  
Catalog # [S1PT4X4FIT](#)

SystemOne, Fire-Rated Poke-Through, 4" Fitting Only, (1) 3/4" EMT for Power, (2) 3/4" EMTs for Low Voltage

### Features

- 4" Fire-Rated Poke-Through
- For use with Universal Flange/Cover Assemblies and Subplates
- (1) 3/4" EMT for Power
- (2) 3/4" EMT Stems for Low Voltage
- Junction Box Sold Separately

### Specifications

Industry Standard(s)	cULus Listed
EU RoHS Indicator	No

### Configuration

Number Of Outlets	(4) 20A, 125V Receptacles, (4) Hubbell Keystone Openings
-------------------	--

### General

Material - Mounting Hardware Specifications	Step-Down Installation <ul style="list-style-type: none"><li>• Approval - Approved for use in the City of Chicago</li></ul>
---	---



- Cover and flange - Powder coat cast aluminum
- Min. floor thickness - 2 1/4 in. (57.2)
- Mounting - 4 in. (101.6) cored concrete Dia. through hole

UPC  
Style  
Application - For Use On

783585371399  
FRPT Fittings  
Carpet/Tile

### Logistics

Carton Quantity	1
Pallet Quantity	55

### Product Assets

[Catalog \[English\]](#)  
[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Catalog Page \[English\]](#)  
[Catalog Page \[English\]](#)