

HUBBELL Premise Wiring

Recessed 4" Series, (1) S1R4PTFIT fitting, (1) S1R4CVRNKL Nickel Plated Recessed Cover, (1) S1R4SPQUAD Sub Plate, (1) S1FRPTJB Hubbell Junction Box

By Hubbell Premise Wiring
Catalog # [S1R4PTQUADNKL](#)

Recessed 4" Series, (1) S1R4PTFIT fitting, (1) S1R4CVRNKL, (1)
S1R4SPQUAD, (1) S1FRPTJB Hubbell Junction Box



Features

- For use with a 4.00" to 4.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

4" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• cULus Listed• Meets ADA Standards• UL 514A Listed
EU RoHS Indicator	Contact Manufacturer
Conductor	
Cable Entry	Through Cover
Configuration	
Number Of Outlets	(1) Quad 20A 125V Receptacle

Dimensions

Size

Standard Sized Product

General

Sub Brand	SystemOne Recessed
Material - Mounting Hardware Type	Mounting Hardware Included 4" Recessed Rated Poke Through Kits
Material	Fabricated
UPC	783585446189
Style	FRPT - Complete Kits
Application - For Use On	Concrete
Color	Nickel
Mounting Type	4" Core Hole

Logistics

Carton Quantity	1
Pallet Quantity	90

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)