

HUBBELL Premise Wiring

Recessed 6" Series, Sub Plate, 50% Right Side, (4) 20A Pre-Wired Receptacles, 1 or 2 Circuits, 25" Leads

By Hubbell Premise Wiring
Catalog # [S1R6SPH25](#)

Recessed 6" Series, Sub Plate, 50% Right Side, (4) 20A Pre-Wired Receptacles, 1 or 2 Circuits, 25" Leads



Features

- Steel Construction
- White Powder Coat Paint
- Includes Necessary Mounting Hardware

Application

6" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s)	cULus Listed
EU RoHS Indicator	Contact Manufacturer

Configuration

Number Of Outlets	(4) 20A Pre-Wired Receptacles, 1 or 2 Circuits, 18" Leads
-------------------	--

Dimensions

Size

Standard Sized Product

General

Sub Brand	SystemOne Recessed
Material - Mounting Hardware Type	Mounting Hardware Included 6" Recessed Rated Poke Through Sub Plates
Material	Fabricated
UPC	783585545028
Style	Sub-Plates
Application - For Use On	Concrete
Color	White
Mounting Type	Screw Mount

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English, Spanish, French\]](#)