

## Temporary Power, Spider Box, 30A 125/250V, 3-Pole 4-Wire Grounding, Locking Receptacles, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [SDTL1A](#)

Temporary Power, Spider Box, 30A 125/250V, 3-Pole 4-Wire  
Grounding, Locking Receptacles, Yellow



### Features

- Spider Box
- 30A 125/250V
- 3-Pole 4-Wire Grounding
- Locking Receptacles

### Application

Heavy Duty Portable

### Specifications

Environmental Conditions	Indoor and Outdoor
EU RoHS Indicator	No
Nema Rating	6) L5-20R, 1) L15-30R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#10 AWG
Number Of Poles	2-Pole

### Current

Phase	Single Phase
-------	--------------

Current / Amperage Rating	30 A
Connectivity	Pre-Wired
Current Rating	30 A
Amperage Rating	30 A
Wattage	3750
Voltage Rating	125 VAC

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### General

Item Type	Twist-Lock® Singles
Material - Mounting Hardware	Non-Mounted, Portable
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Thermoplastic
UPC	783585128702
Color	Yellow

### Product Assets

[Catalog \[English\]](#)

[Installation Manual \[Spanish, French, English\]](#)