

Kellems Wire Management, Cord Connectors, European Style .25-.48", 3/4", Gray

By Hubbell Wiring Device-Kellems
Catalog # [SEC75RGA](#)

Kellems Wire Management, Cord Connectors, European Style
.25-.48", 3/4", Gray



Features

- European Style .25-.48"
- 3/4"
- Gray

Application

Straight Male

Performance

Flammability - UL 94X-2

Specifications

Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none">• UL Listing File E-41567, UL Recognition File E-41567• CSA File LR27378C, VDE Marks Licence #136681
Nema Rating	IP66

Conductor

Number Of Conductors Single

Conductor Range 0.25-0.48 in (6.35-12.19 mm)

Dimensions

Display Size 3/4" NPT

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Gray
Material - Mounting Hardware Type	Locknut or Tapped Opening Low Profile NPT Cord Connectors
Material	Nylon
UPC	783585346915

Logistics

Carton Quantity 50

Operational

Temperature Rating	Minimum -22°F to 225°F (-30°C to 107°C).
Operating Temperature	-22 Deg F to 225 Deg F (-30 Deg C to 107 Deg C)

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)