

Straight Blade Devices
15A, 125V, 2 Pole, 3 Wire Grounding
USB Charger Receptacles



Features

- Two USB ports 3 Amp, 5V DC, type A, class 2.0
- Tamper-Resistant decorator duplex receptacle
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

Resources

[eCatalog](#)

Ordering Information

Description	Device Color		Catalog Number
SNAPConnect USB 15A 125V AC Charger, Tamper-Resistant Style Line® decorator duplex receptacle, two USB type 2.0 ports 3 Amp, 5 Volt DC	Light Almond	883778305382	SNAP15USBLA

Listings

UL1310 (SNAPConnect®)
cETLus listed to UL498

Specifications

Face	RTP
Base	RTP
LED	Green Indicator
Contacts	Plated Copper
Mounting Strap	Galvanized steel
Auto Self-grounding staple	Stainless steel
Mounting Screws	Zinc plated steel
USB Port	Stainless Steel

Performance

Electrical

Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Port	Stainless steel Rated for 10,000 plug insertions and removal

Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)

