

SNAPConnect® Extra Heavy Duty Receptacle

HUBBELL


- Audible SNAP, indicates solid connection
- Reduces installation time
- Tamper-Resistant, Split Circuit
- Assembled in USA

Description	Device Color	UPC Number	Catalog Number
Tamper-Resistant, Split Circuit	Gray	783585551791	SNAP2162GYCTR A



UL Listed to UL498 File No. E2265
 Certified to CSA, C22.2, No. 42 File 364
 Fed. Spec. W-C-675
 NEMA® WD-6 Compliant

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass



Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Product Identification Ratings are a permanent part of the device

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)

Wallplate or Weatherproof Cover Opening

Customer Sales Drawing
eCatalog
Installation Instructions

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

