

Straight Blade Devices

15 Amp, 125 Volt, 2-Pole, 3-Wire

SNAPConnect[®] Extra Heavy Duty Receptacle



- Features
- Audible SNAP, indicates solid connection
 - Reduces installation time
 - Requires minimal box space
 - Assembled in USA

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Standard Duplex	Red	783585540481	SNAP5262RNA




Listings

UL Listed to UL498 File No. E2402
Certified to CSA, C22.2, No. 42 File 501
Fed. Spec. W-C-812
NEMA[®] WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass



Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical	
Product Identification	Ratings are a permanent part of the device

Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)

Complementary Products

Wallplate or Weatherproof Cover
Opening

Online Resources

Customer Sales Drawing
eCatalog
Installation Instructions

