

Straight Blade Devices

20 Amp, 125 Volt, 2-Pole, 3-Wire

SNAPConnect[®] Permanently Marked Receptacle



- Features**
- Audible SNAP, indicates solid connection
 - Reduces installation time
 - Split Circuit, Half Controlled
 - Power symbol is clearly visible

Ordering Information

Description	Device Color	UPC Number	Catalog Number
One Controlled Face, Split Circuit	Lt Almond	78358555294	SNAP5362C1LA



Listings

UL Listed to UL498 File No. E2426
Certified to CSA, C22.2, No. 42 File 525
Fed. Spec. W-C-836
NEMA[®] WD-6 Compliant

Complementary Products

Wallplate or Weatherproof Cover
Opening

Specifications

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass

Online Resources

eCatalog

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)

