

Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

Extra Heavy Duty SNAPconnect® Standard Duplex Receptacles for Controlled Applications



- Features
- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
 - Patented TR design eliminates plug-in difficulty and TR complaints
 - Markings can be read regardless of mounting orientation
 - Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
 - Complements Hubbells Load Logic control system or other available energy management system



Ordering Information

Description	Device Color	UPC Number	Catalog Number
SNAPconnect® Standard Duplex Smooth nylon face	Brown	783585583419	SNAP5362C1TRA

Listings

UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42 File 285
Fed. Spec. W-C-596
NEMA® WD-6 Compliant

Online Resources

eCatalog

Specifications

Face	Nylon
Base	PBT
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Galvanized steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)

