

## Straight Blade Devices

20A, 250V, 2 Pole, 3 Wire Grounding

# Extra Heavy Duty SNAPconnect® Single Receptacle

# HUBBELL

## Features

- Audible SNAP indicates solid connection
- Reduces installation time
- Fully insulated design

## Ordering Information

Description	Device Color	UPC Number	Catalog Number
Specification grade, smooth nylon face	Light Almond	783585531021	<b>SNAP5461LATR</b>

## Listings

UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42 File 285  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

## Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Galvanized steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel

## Performance

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)
Product Identification	Ratings are a permanent part of the device



## Complementary Products

Stranded SNAPconnector	SNAP252RA
Solid SNAPconnector	SNAP251RA

## Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

