

Straight Blade Devices

15A, 250V, 2 Pole, 3 Wire Grounding

Extra Heavy Duty SNAPconnect® Single Receptacle



- Features
- Audible SNAP indicates solid connection
 - Reduces installation time
 - Fully insulated design

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Specification grade, smooth nylon face	Black	783585531106	SNAP5661BKTR

Listings

UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42 File 285
Fed. Spec. W-C-596
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Galvanized steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc plated steel

Performance

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)
Product Identification	Ratings are a permanent part of the device



Complementary Products

Stranded SNAPconnector	SNAP252RA
Solid SNAPconnector	SNAP251RA

Online Resources

eCatalog

