

# Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding USB Charger Receptacles

# HUBBELL

## Features

- Two USB ports 3 Amp, 5V DC, type A, class 2.0
- Tamper-Resistant decorator duplex receptacle
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

## Resources

[eCatalog](#)

## Ordering Information

Description	Device Color		Catalog Number
Hospital Grade SNAPConnect® USB 15A 125V AC Charger Tamper-Resistant Receptacle, two USB type 2.0 ports 3 Amp, 5 Volt DC	Ivory	883778305481	SNAP8200USBI

## Listings

UL1310 (SNAPConnect®)  
cETLus listed to UL498

## Specifications

Face	RTP
Base	RTP
LED	Green Indicator
Contacts	Plated Copper
Mounting Strap	Galvanized steel
Auto Self-grounding staple	Stainless steel
Mounting Screws	Zinc plated steel
USB Port	Stainless Steel

## Performance

### Electrical

Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
USB Port	Stainless steel Rated for 10,000 plug insertions and removal

### Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

