

## Straight Blade Devices

15 Amp, 125 Volt, 2-Pole, 3-Wire

# SNAPConnect<sup>®</sup> Hospital Grade Receptacle

# HUBBELL

### Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Tamper Resistant, Single Receptacle
- Assembled in USA

### Ordering Information

Description	Device Color	UPC Number	Catalog Number
Hospital Grade, Standard Duplex	Brown	783585557540	SNAP8210TR

### Listings

UL Listed to UL498 File No. E2517  
Certified to CSA, C22.2, No. 42 File 616  
Fed. Spec. W-C-927  
NEMA<sup>®</sup> WD-6 Compliant

### Specifications

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass

### Performance

#### Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

#### Mechanical

Product Identification	Ratings are a permanent part of the device
------------------------	--

#### Environmental

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)



### Complementary Products

Wallplate or Weatherproof Cover  
Opening

### Online Resources

Customer Sales Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

