

Straight Blade Devices, SNAPConnect® Tester, Circuit Tester for SNAPConnect® receptacle terminals, GFCI and standard receptacles

By Hubbell Wiring Device-Kellems
Catalog # [SNAPCTG](#)



Straight Blade Devices, SNAPConnect® Tester, Circuit Tester for SNAPConnect® receptacle terminals, GFCI and standard receptacles

Features

- 3-in-1 Design. Tests proper wiring of SNAPConnect® receptacles, Tests proper wiring of standard receptacles, tests GFCI receptacles

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186

Conductor

Number Of Wires	3-Wire
Number Of Conductors	3-Wire Grounding
Number Of Poles	2-Pole

Current

Dielectric Strength	Withstands 2,000V minimum
Voltage Rating Description	125 V
Connectivity	Connectorized
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	4.76 in
Weight	0.25 lb.
Height	1.44 in

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Type	Circuit Tester
Material	Nylon
UPC	783585555751

Logistics

Carton Quantity	10
Pallet Quantity	1120

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
-----------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)