

## SNAPConnect® Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle, 15A, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGF15GRY](#)

Straight Blade Devices, SNAPConnect®, AUTOGUARD®, Self-Test,  
GFCI Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray



### Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

### Application

Commercial Grade

### Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

### Conductor

Wire Size	SNAPConnect®
-----------	--------------

### Current

Phase	Single Phase
Current / Amperage Rating	15 A
Wattage	1875 W
Voltage Rating	125 VAC

### Dimensions

Size	4.12 in x 1.75 in x 1.48 in
------	-----------------------------

Width	1.75 in
Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

### General

Item Type	Style Line GFCI Receptacle
Type	Standard
Series	Heavy Duty
Material	Nylon
Specifications	<ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Contacts - Brass</li><li>• Mounting Screws - Stainless Steel</li><li>• Mounting Strap - Galvanized Steel</li><li>• Power Contacts - Brass</li></ul>
UPC	783585746340
Color	Gray

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Catalog Page \[English\]](#)