

SNAPConnect® Heavy Duty Commercial
AUTOGUARD® Self-Test GFCI Receptacle,
20A, Red

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGF20R](#)

Straight Blade Devices, SNAPConnect®, AUTOGUARD®, Self-Test,
GFCI Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Red

Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

Commercial Grade

Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

Conductor

Wire Size	SNAPConnect®
-----------	--------------

Current

Phase	Single Phase
Current / Amperage Rating	20 A
Wattage	2500 W
Voltage Rating	125 VAC

Dimensions

Size	4.12 in x 1.75 in x 1.48 in
------	-----------------------------



Width	1.75 in
Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

General

Item Type	Style Line GFCI Receptacle
Type	Standard
Series	Heavy Duty
Material	Nylon
Specifications	• Base - Nylon • Face - Nylon • Contacts - Brass • Mounting Screws - Stainless Steel • Mounting Strap - Galvanized Steel • Power Contacts - Brass
UPC	783585746432
Color	Red

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)