

## SNAPConnect® Heavy Duty Hospital Grade AUTOGUARD® Self-Test GFCI Receptacle, 15A, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGF82I](#)

SNAPConnect® Straight Blade GFCI Hospital Grade Receptacle,  
15A



### Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

### Application

Commercial Hospital Grade

### Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

### Conductor

Wire Size	SNAPConnect®
-----------	--------------

### Current

Phase	Single Phase
Current / Amperage Rating	15 A
Wattage	1875 W
Voltage Rating	125 VAC

### Dimensions

Size	4.12 in x 1.75 in x 1.48 in
Width	1.75 in

Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

### General

Item Type	Self test GFCI receptacle
Type	Standard
Series	Hospital Grade
Material	Nylon
Specifications	<ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Contacts - Brass</li><li>• Mounting Screws - Stainless Steel</li><li>• Mounting Strap - Brass</li><li>• Power Contacts - Brass</li></ul>
UPC	783585746456
Color	Ivory

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)