

Ground Fault Products

Commercial Hospital Grade Standard GFCI Receptacles



Features

- Audible SNAP, indicates solid connection
- Triple wipe construction
- Patented AUTOGUARD® self test technology
- Green power indicator and red trip indicator

Ordering Information

Description	Color	UPC	Catalog Number
15A, 125V, Style Line®, hospital grade, SNAPConnect®, AUTOGUARD® self test GFCI receptacle	White	783585746487	SNAPGF82W

Listings

UL Listed - Canadian and U.S.
Meets ADA Standards
Meets all NEC® requirements
CSA Certified
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Brass
Mounting Screws	Zinc plated steel

Performance

Electrical	
Amperage	15A/20A, 20A Feed Thru
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Frequency	60 Hz
Maximum Interrupting Capacity	10,000A
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Voltage	120V AC +10% - 15% (102V to 132V)
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	UL 94V-2
Operating Temperature	-35°C to 66°C or -30°F to 150°F



Related Products

Wallplates for duplex openings	Solid Right Angle Pigtailed Terminal
SNAP1RA	Stranded Right Angle Pigtailed Terminal
SNAP2RA	

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

