

SNAPConnect® Heavy Duty Hospital Grade
AUTOGUARD® Self-Test GFCI Receptacle,
20A, Gray

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGF83GRY](#)

SNAPConnect® Straight Blade GFCI Hospital Grade Receptacle,
20A

Features

- Audible SNAP, indicates solid connection
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

Commercial Hospital Grade

Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

Conductor

Wire Size	SNAPConnect®
-----------	--------------

Current

Phase	Single Phase
Current / Amperage Rating	20 A
Wattage	2500 W
Voltage Rating	125 VAC

Dimensions

Size	4.12 in x 1.75 in x 1.48 in
Width	1.75 in



Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

General

Item Type	Self test GFCI receptacle
Type	Standard
Series	Hospital Grade
Material	Nylon
Specifications	• Base - Nylon • Face - Nylon • Contacts - Brass • Mounting Screws - Stainless Steel • Mounting Strap - Brass • Power Contacts - Brass
UPC	783585746517
Color	Gray

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)