

## SNAPConnect® Heavy Duty Commercial Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGFTW15I](#)

Straight Blade Devices, SNAPConnect®, Weather and Tamper-Resistant, AUTOGUARD®, Self-Test, GFCI Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory



### Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

### Application

Commercial Grade

### Specifications

|                          |  |
|--------------------------|--|
| Industry Standard(s)     | UL 943 and Meets All NEC® Requirements |
| Environmental Conditions | Weather Resistant                      |
| Nema Rating              | 5-15R                                  |

### Conductor

|           |              |
|-----------|--------------|
| Wire Size | SNAPConnect® |
|-----------|--------------|

### Current

|                           |              |
|---------------------------|--------------|
| Phase                     | Single Phase |
| Current / Amperage Rating | 15 A         |
| Wattage                   | 1875 W       |
| Voltage Rating            | 125 VAC      |

### Dimensions

|            |                             |
|------------|-----------------------------|
| Size       | 4.12 in x 1.75 in x 1.48 in |
| Width      | 1.75 in                     |
| Height     | 4.12 in                     |
| Length     | 1.48 in                     |
| Dimensions | 1.48 in x 1.75 in x 4.12 in |

### General

|                |   |
|----------------|---|
| Item Type      | Style Line GFCI Receptacle<br>Tamper-Resistant, Weather<br>Resistant  |
| Type           |   |
| Series         | Heavy Duty  |
| Material       | Nylon   |
| Specifications | <ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Contacts - Brass</li><li>• Mounting Screws - Stainless Steel</li><li>• Mounting Strap - Galvanized Steel</li><li>• Power Contacts - Brass</li></ul> |
| UPC            | 783585746135  |
| Color          | Ivory   |

### Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Catalog Page \[English\]](#)