

SNAPConnect® Heavy Duty Commercial
Tamper-Resistant/Weather Resistant
AUTOGUARD® Self-Test GFCI Receptacle,
20A, Brown

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGFTW20](#)

Straight Blade Devices, SNAPConnect®, Weather and Tamper-Resistant, AUTOGUARD®, Self-Test, GFCI Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown

Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

Commercial Grade

Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Environmental Conditions	Weather Resistant
Nema Rating	5-20R

Conductor

Wire Size	SNAPConnect®
-----------	--------------

Current

Phase	Single Phase
Current / Amperage Rating	20 A
Wattage	2500 W
Voltage Rating	125 VAC

Dimensions

Size	4.12 in x 1.75 in x 1.48 in
Width	1.75 in
Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

General

Item Type	Style Line GFCI Receptacle Tamper-Resistant, Weather Resistant
-----------	--

Series	Heavy Duty
Material	Nylon

Specifications	• Base - Nylon • Face - Nylon • Contacts - Brass • Mounting Screws - Stainless Steel • Mounting Strap - Galvanized Steel • Power Contacts - Brass
UPC	783585746166
Color	Brown

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)

