

## SNAPConnect® Heavy Duty Commercial Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [SNAPGFTW20I](#)

Straight Blade Devices, SNAPConnect®, Weather and Tamper-Resistant, AUTOGUARD®, Self-Test, GFCI Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory



### Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

### Application

Commercial Grade

### Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Environmental Conditions	Weather Resistant
Nema Rating	5-20R

### Conductor

Wire Size	SNAPConnect®
-----------	--------------

### Current

Phase	Single Phase
Current / Amperage Rating	20 A
Wattage	2500 W
Voltage Rating	125 VAC

### Dimensions

Size	4.12 in x 1.75 in x 1.48 in
Width	1.75 in
Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

### General

Item Type	Style Line GFCI Receptacle Tamper-Resistant, Weather Resistant
Type	
Series	Heavy Duty
Material	Nylon
Specifications	<ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Contacts - Brass</li><li>• Mounting Screws - Stainless Steel</li><li>• Mounting Strap - Galvanized Steel</li><li>• Power Contacts - Brass</li></ul>
UPC	783585746180
Color	Ivory

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Catalog Page \[English\]](#)