

SNAPConnect® Heavy Duty Hospital Grade Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Light Almond

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGFTW83LA](#)

Straight Blade SNAPConnect® WRTR GFCI Hospital Grade
Receptacle, 20A



Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

Commercial Hospital Grade

Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Environmental Conditions	Weather Resistant
Nema Rating	5-20R

Conductor

Wire Size	SNAPConnect®
-----------	--------------

Current

Phase	Single Phase
Current / Amperage Rating	20 A
Wattage	2500 W
Voltage Rating	125 VAC

Dimensions

Size	4.12 in x 1.75 in x 1.48 in
------	-----------------------------

Width	1.75 in
Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

General

Item Type	Self test GFCI receptacle Tamper-Resistant, Weather Resistant
Type	Hospital Grade
Series	Nylon
Material	Nylon
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Contacts - Brass• Mounting Screws - Stainless Steel• Mounting Strap - Brass• Power Contacts - Brass
UPC	783585746319
Color	Light Almond

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)