

HUBBELL Premise Wiring

Wallplates and Boxes, Metallic Plates, 2-Gang, 2) GFCI Openings, Standard Size, Stainless Steel

By Hubbell Premise Wiring
Catalog # [SS262](#)

Wallplates and Boxes, Metallic Plates, 2- Gang, 2) GFCI Openings, Standard Size, Stainless Steel

Features

- Environments subjected to heavy abuse
- Ideal for highly corrosive environments
- Magnetic: 17.0% Chromium, Less than 0.5% Nickel
- Finish is lacquer coated to inhibit oxidation

Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

Specifications

| | |
|------------------------------------|-----------|
| Industry Standard(s) | UL Listed |
| EU RoHS Indicator | Yes |
| Standards - RoHS Compliance Status | CM |

Configuration

| | |
|-------------------|----------------|
| Orientation | Vertical Mount |
| Number of Gang(s) | 2-Gang |

Dimensions

| | |
|-----------|---------|
| Size | 2-Gang |
| Weight | 0.1 lb. |
| Thickness | 0.04 |

General



Material - Mounting Hardware Type
Material Specifications

Screw Mounting Plates

Stainless Steel

- Appearance - Horizontal brushed appearance
 - Material - Stainless steel 302/304
 - Mounting Screws - 302/304 SS, Slotted head
 - Plate Openings - Decorator
 - Plate Type - 2-Gang
- UPC
883778201677

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 8000 |

Operational

| | |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85 °C |
|-----------------------|----------------|

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)