

Switches and Lighting Control, Occupancy Sensor Switch, Decorator, 8A 120/277V AC, White

By Hubbell Wiring Device-Kellems
Catalog # [WLS1278W](#)

Switches and Lighting Control, Occupancy Sensor Switch, Decorator, 8A 120/277V AC, White

Features

- Wall Switches

Application

Compatible with most LED and CFL

Performance

Electrical - Indication - Green indicator light, Electrical - Operating voltage - 120/277V, 50/60Hz, Environment - Operating Environment - Indoor use only, Environment - Operating temperature - 32°F to 104°F (0°C to 40°C), Environment - Range - RF range is 30 ft (10m) obstructed, 60 ft (18m) line of sight, Environment - Relative humidity - 0% to 90% humidity, non-condensing, Mechanical - Capacity - Up to 9 WLAS accessory switches can be configured to work together with one WLS1278, Mechanical - Wire Size - #20 to 16 AWG (0.5 to 1.5mm²) solid or stranded wire

Specifications

EU RoHS Indicator	No
Industry Standard(s)	UL Listed



Current

Current Rating	8 A
Amperage Rating	8 A
Voltage Rating Description	120/277V AC
Current / Amperage Rating	8 A
Voltage Rating	120/277 VAC

General

Series	Passive Infrared
Style	Accessories
Color	White
Type	<ul style="list-style-type: none">• Wireless - Ceiling Mount• Wireless - Wall Mount
Specifications	Warranty - 1 year
UPC	783585159485

Logistics

Carton Quantity	24
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)