

Adapter, 2-30A TO 1-50A 125/250V

By Hubbell Wiring Device-Kellems
Catalog # [YQ230](#)

Adapter, 2-30A TO 1-50A



Features

- Sealing grommets keep moisture out
- UV resistant high-impact housing
- Cord clamps prevent strain on terminals

Application

Marine Grade

Specifications

Environmental Conditions	Indoor/Outdoor
EU RoHS Indicator	No
Standards - RoHS Compliance	CM
Status	
Nema Rating	2) L5-30P to 50A Non-NEMA

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#10 AWG
Number Of Poles	2-Pole

Current

Current Rating	30 A
Amperage Rating	30 A
Phase	Single Phase
Current / Amperage Rating	30 A
Connectivity	Plug Together
Wattage	7500
Voltage Rating	125/250 VAC

Dimensions

Display Size Standard Sized Product

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	Yellow
Item Type	Y-Adapter
Material - Mounting Hardware	Plug Together
Material	Thermoplastic
Specifications	<ul style="list-style-type: none">• Adapter Style - Intelligent Y Type• Female End Rating - 50A, 125/250V, 3P4W Twist-Lock®• Male End Rating - 30A, 125V, 2P3W Twist-Lock®• Poles and Wires - Male Side- 2P, 3W Grounding, Female Side- 3P 4W Grounding• Product Type - Adapters
UPC	783585831305

Logistics

Carton Quantity 1

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)