

POWER CUTTERS

## Husqvarna K 970



1/11



**OUTPUT POWER**

4.8 kW

**CUTTING DEPTH, MAX**

155 mm

**BLADE DIAMETER, MAX**

400 mm

**WEIGHT (COMPLETE PRODUCT W/O SIDE PACKED ARTICLES)**

11.6 kg

**PRODUCT VARIANT**

POWER CUTTER K 970 16" | 20mm/1"  
Art nr: 967 34 81-01

### PRODUCT DESCRIPTION

Sturdy, reliable, light and powerful - the K 970 disc cutter is ready to perform when you are. The ultimate choice when you need an all-round cutter performing in the toughest conditions, withstanding climate and fuel variations. Suitable for road works when used with the corresponding KV 970 trolley. The trolley also means you can fully concentrate on the cutting job.

## ALL PRODUCTS SPECIFICATION

K 970

K 970 14" | 20MM/1"

967 34 80-01

K 970 16" | 20MM/1"

967 34 81-01

### ENGINE

Output power	4.8 kW	4.8 kW
Cylinders	1	1
Number of strokes	2-stroke engine	2-stroke engine
Exhaust emissions (CO <sub>2</sub> EU V) <sup>Ⓞ</sup>	736 g/kWh	736 g/kWh
Power source	Petrol	Petrol

### CUTTING EQUIPMENT

Cutting depth, max	125 mm	155 mm
Blade diameter, max	350 mm	400 mm
Arbor diameter	25.4/20 mm	25.4/20 mm
Blade thickness, max	5 mm	5 mm
Peripheral speed, max	90 m/s	90 m/s
Coolant	Wet	Wet

### DIMENSIONS

Product size length	661 mm	688 mm
Product size width	214 mm	214 mm
Product size height	444 mm	481 mm
Weight (complete product w/o side packed articles)	11 kg	11.6 kg

### SOUND AND NOISE

Sound power level, guaranteed (LWA)	115 dB(A)	115 dB(A)
Sound pressure level at operators ear	104 dB(A)	104 dB(A)

### VIBRATION

Vibrations left/front handle	3.8 m/s <sup>2</sup>	3.5 m/s <sup>2</sup>
Vibrations right/rear handle	4.2 m/s <sup>2</sup>	4 m/s <sup>2</sup>

## DIAMOND TOOLS

GOLD



POWER CUTTER  
BLADES  
**ELITE-CUT  
S35 EXO-  
GRIT™**

2 variants  
Diameter mm  
**350 / 400 mm**  
Segment height mm  
**15 mm**  
Arbor diameter  
**25.4/20 mm**

GOLD



POWER CUTTER  
BLADES  
**ELITE-CUT  
S45 EXO-  
GRIT™**

3 variants  
Diameter mm  
**300 / 350 / 400 mm**  
Segment height mm  
**15 mm**  
Arbor diameter  
**20 mm / 25.4/20 mm**

GOLD



POWER CUTTER  
BLADES  
**ELITE-CUT  
S65 EXO-  
GRIT™**

3 variants  
Diameter mm  
**300 / 350 / 400 mm**  
Segment height mm  
**15 mm**  
Arbor diameter  
**20 mm / 25.4/20 mm**

GOLD  
NEW



POWER CUTTER  
BLADES  
**ELITE-CUT  
S85**

3 variants  
Diameter mm  
**300 / 350 / 400 mm**  
Segment height mm  
**12 mm**  
Arbor diameter  
**25.4/20 mm**

## ACCESSORIES



### WATER TANKS **WT 15i**

2 variants

Water pressure, max  
**0.9 / 1 bar**  
Water tank capacity  
**15 l**  
Hose length  
**3 m**  
Weight (complete product ...  
**3.6 kg**



### CUTTING TROLLEYS **KV 9 / 12**

Accessory for  
**Power cutters**



### CUTTING TROLLEYS **KV 9 / 12**

Accessory for  
**Power cutters**



### ATTACHMENTS **Wheel kit**

Accessory for  
**Power cutters**