

Portable Outdoor Timer - Two-Circuit Portable Outdoor Timer

Item P1261P



PRODUCT DESCRIPTION

Use these convenient plug-in timers instead of hard-wired controls. They offer plug-in receptacles for convenience and ease of use. They have built-in GFCI protected circuits.

FEATURES

- ▶ 24-hour with 23 ½-hour MAX ON time
- ▶ Timed circuit controlled by timer
- ▶ Timed and photocontrol circuit controlled by photocell and timer (P1251P only)
- ▶ Built-in GFCI protected circuits and three-prong grounded plug for time switch supply
- ▶ Type 3R plastic indoor/outdoor enclosure
- ▶ 2 ON/OFF trippers standard
- ▶ Accepts up to 12 sets of trippers

APPLICATIONS

- ▶ Landscape Lighting
- ▶ Motor Control
- ▶ Pump Control

TECHNICAL DATA

General	
Model Number	P1261P
Description	Two-Circuit Portable Outdoor Timer
UPC Code	078275067530
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	1-Year limited

Control Specifications	
Operation Mode	24 hour

Mechanical Specifications	
Plug Configurations	5-15
Enclosure Type	Indoor/outdoor type 3R plastic

Dimensions	
Product Dimensions (H x W x D) in	9.375 x 5.5 x 4 in
Cord Size	3 wire, outdoor grade, 24" with grounded plug
Cord Length (ft)	2
Cord Length (m)	0.61

Load Ratings	
Motor	1 HP, 15 FLA, 90 LRA @ 120 VAC

Packaging	
Unit Carton Dimensions (H x W x L) in	10.5 x 7 x 4 in

Standards and Certifications

CSA Certification cCSAus

California Proposition 65 DEHP

ACCESSORIES



107TN221

Red (OFF) tripper for TN, PB, TB Series, P1101, P1131, P1161, P1261P, AL300TPWS, AL600TPWS and AL900TPWS



107TN222

Turquoise (ON) tripper for TN, PB, TB Series, P1101, P1131, P1161, P1261P, AL300TPWS, AL600TPWS and AL900TPWS