

Mechanical Time Switch - 7-Day 120V Mechanical Panel Mount Timer, 56 Trippers

Item PB873MKZ



PRODUCT DESCRIPTION

These timers provide automatic control for pumps, cleaners and other types of loads. Timers have three-way mounting; flush in round opening, raised in rectangular opening or on base. Quick connect terminals for easy installation.

FEATURES

- ▶ Automated control for pumps, cleaners and other types of loads
- ▶ 3 different mounting methods
- ▶ Quick connect terminals for easy installation
- ▶ 24-hour timing cycle - MIN ON time 1-hr, MAX ON time 23-hr, 30-min intervals
- ▶ 7-day timing cycle - 6 to 162-hr ON time, 3-hr intervals

APPLICATIONS

- ▶ Motor Control
- ▶ Pump Control

TECHNICAL DATA

General

Model Number	PB873MKZ
Description	7-Day 120V Mechanical Panel Mount Timer, 56 Trippers
UPC Code	078275701489
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	1-Year limited

Control Specifications

Operation Mode	7 day
----------------	-------

Mechanical Specifications

Captive Trippers	56
------------------	----

Dimensions

Product Dimensions (H x W x D) in	3.333 x 2.813 x 1.953 in
-----------------------------------	--------------------------

Material Specifications

Color	Black
-------	-------

Load Ratings

Resistive Load Ratings Ranges	20 A, 120-277 VAC, 60 Hz
Pilot Duty Load Ratings Ranges	360 VA, 120-240 VAC, 60 Hz
Motor Load Ratings Ranges	1 HP, 16 FLA @ 120 VAC, 60 Hz; 2 HP, 12 FLA @ 240 VAC, 60 Hz

Electrical Specifications

Wiring Option	Terminals; (4) 1/4" male (2) for load (2) for independent clock motor
Input Voltage Range(s)	120 VAC, 60 Hz

Number of Circuits	1
--------------------	---

Switch Type	SPST
-------------	------

Packaging

Shipping Weight (lbs)	0.429
-----------------------	-------

Unit Carton Dimensions (H x W x L) in	4 x 2.75 x 3 in
---------------------------------------	-----------------

Standards and Certifications

UL Certification	UL
------------------	----

Other Certifications and Compatibilities	Green Energy
------------------------------------------	--------------

California Proposition 65	None
---------------------------	------

RoHS Certification	X
--------------------	---

ACCESSORIES



156PB10398A

Trippers - Clip, ON/OFF, 24-Hr for PB and PF1100 Series



107TN221

Red (OFF) tripper for TN, PB, TB Series, P1101, P1131, P1161, P1261P, AL300TPWS, AL600TPWS and AL900TPWS



107TN222

Turquoise (ON) tripper for TN, PB, TB Series, P1101, P1131, P1161, P1261P, AL300TPWS, AL600TPWS and AL900TPWS