

Item Bundle - Pool/Spa Remotely Operated Combination Control System

Item RC2163BFE



PRODUCT DESCRIPTION

Control ON/OFF timing of pool/spa loads remotely, away from the water. Includes actuators for turning valves between pool and spa modes.

FEATURES

- ▶ Eight breaker spaces
- ▶ Use spring wound timer, toggle switch, wireless receiver/transmitter or Ascend™ Smart In-Wall timer to operate equipment
- ▶ 3-Wire heater control
- ▶ Digital override timer for spa mode
- ▶ (2) PE24VA 24-V valve actuators included
- ▶ Heavy-duty Type 3R metal indoor/outdoor load center

APPLICATIONS

- ▶ Heater Thermostat Control
- ▶ Motor Control
- ▶ Pump Control

TECHNICAL DATA

General

Model Number	RC2163BFE
Description	Pool/Spa Remotely Operated Combination Control System
UPC Code	078275088245
Brand	Intermatic
Country of Origin (Intermatic)	TAIWAN
Warranty Period	1-Year limited

Control Specifications

Number Of Heaters Controlled	1
Number of Actuators Included	2

Mechanical Specifications

Number of Breaker Knockouts	8
Enclosure Type	Outdoor type 3R plastic

Dimensions

Product Dimensions (H x W x D) in	16.875 x 10.875 x 4.75 in
-----------------------------------	---------------------------

Material Specifications

Color	Beige
-------	-------

Load Ratings

Motor Load Ratings Single Speed	1 1/2 HP @ 120 VAC, 3 HP @ 240 VAC, 60 Hz
Load Center Rating Display	100 A, 120/240 VAC or 120/208 VAC, Single Phase, 60 Hz

Electrical Specifications

Number of Circuits	1
Switch Type	SPST (not included)
Number of Actuators Controlled	3

Packaging

Shipping Weight (lbs)	24.948
Unit Carton Dimensions (H x W x L) in	10.5 x 13.88 x 19.5 in

Standards and Certifications

CSA Certification	cCSAus
California Proposition 65	DEHP

ACCESSORIES



21T166A

Spacer-Standoff, 3" long - 2 pack