

## Item Bundle - 100 A Load Center with 300 W Transformer and T103M Mechanism, 8-Breaker Spaces

Item T40003RT3



### PRODUCT DESCRIPTION

These mechanical control systems include built-in transformers for ease of installation.

### FEATURES

- ▶ Load Centers have eight breaker spaces
- ▶ All-in-one control power for pool/spa installation
- ▶ Easy to wire
- ▶ Can house additional Intermatic mechanisms and components
- ▶ Control two-speed pumps with the T40604RT3
- ▶ Heavy-duty Type 3R metal indoor/outdoor power and load center
- ▶ Wiring devices may be installed in these Load Centers with the use of Standoffs, sold separately
- ▶ Knockout on the side for additional wiring device

### APPLICATIONS

- ▶ Distribution/Control Panel
- ▶ Landscape Lighting
- ▶ Motor Control
- ▶ Pump Control
- ▶ Underwater Lighting

### TECHNICAL DATA

#### General

Model Number	T40003RT3
Description	100 A Load Center with 300 W Transformer and T103M Mechanism, 8-Breaker Spaces
UPC Code	078275061675
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	1-Year limited

#### Mechanical Specifications

Number of Breaker Knockouts	8
Enclosure Type	Outdoor type 3R plastic

#### Dimensions

Product Dimensions (H x W x D) in	20.875 x 12.875 x 4.75 in
Knockout Dimensions Bottom	(5) 7/8" - 1 7/8", (4) 7/8", (2) 1 1/8" - 1 3/8" - 1 5/8"
Knockout Dimensions Back	(4) 7/8" - 1 1/8", (2) 1 1/8" - 1 3/8"
Knockout Dimensions Left	(2) 7/8" - 1 1/8"
Knockout Dimensions Right	(1) 1 3/4" x 2 3/4"

#### Load Ratings

Tungsten Range(s)	40 A, 120-240 VAC, 60 Hz
Inductive	40 A, 240 VAC, 60 Hz; 40 A, 208 VAC, 60 Hz; 40 A, 120 VAC, 60 Hz
Motor	2 HP, 24 FLA @ 120 VAC, 60 Hz; 5 HP, 28 FLA @ 240 VAC, 60 Hz
Load Center Ratings	100 A, 120-208 VAC, 60 Hz; 100 A, 240 VAC, 60 Hz, Single Phase

Resistive Load Ratings Ranges	40 A, 120-240 VAC, 60 Hz
Inductive Load Ratings Ranges	40 A, 120-240 VAC, 60 Hz
Pilot Duty Load Ratings Ranges	1000 VA, 120-240 VAC, 60 Hz
Load Center Rating Display	100 A, 120-240 VAC, Single Phase, 60 Hz
Mechanism Supply Voltage	120 VAC, 60 Hz

#### Electrical Specifications

Number of Circuits	1
Switch Type	DPST
Maximum Power Consumption (W)	3 W
Transformer (W)	300
Transformer Input Voltage	3 A, 120 VAC, 60 Hz
Transformer Output Voltage	12, 13, 14 VAC
Number of Receptacle/Switch Knockouts	1

#### Packaging

Unit Carton Dimensions (H x W x L) in	6.751 x 14.251 x 22.001 in
---------------------------------------	----------------------------

#### Environmental Specifications

Temperature (operation)	-40 °F to 130 °F / (-40 °C to 54 °C)
-------------------------	--------------------------------------

#### Standards and Certifications

CSA Certification	cCSAus
California Proposition 65	Lead

---

## ACCESSORIES



156T1978AMX  
1 Set of ON/OFF Trippers for T100, T7000,  
and WH40



156T1978A  
Extra/replacement trippers 1 ON and 1 OFF



21T166A  
Spacer-Standoff, 3" long - 2 pack



21T156A  
Spacer-Standoff, 3" long - 4 pack



ET-NF  
RC Snubber Noise Filter 24-277VAC/DC for  
Electronic Controls



22T338GR  
Mounting Bracket for Intermatic Standardized  
Timer Mechanisms