

Weather Proof Cover - Extra-Duty Die-Cast In-Use Weatherproof Cover, Single-Gang, Vrt, 2.75" Gray

Item WP3110MXD



PRODUCT DESCRIPTION

Die-Cast In-Use Aluminum Weatherproof Covers are extra-duty rated and easy to install. Heavy-duty die-cast aluminum construction ensures long-lasting durability. Covers come with a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

FEATURES

- ▶ Complies with 2020 NEC Article 406.9 (B)(1) for wet locations and extra-duty applications
- ▶ CEC Article 26-702 Compliant
- ▶ UL Certified for Type 3R outdoor enclosures
- ▶ Meets requirements for cold impact testing: -60° F (-51° C)
- ▶ Heavy-duty die-cast aluminum cover and mounting base with UV stabilized polycarbonate inserts
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws
- ▶ Lockable hasp: All models accept up to 1/4" (6 mm) dia shank
- ▶ Impact rated: 12 lbf. impact test to ensure cover remains intact
- ▶ Reinforced hinge pin designed to exceed 40 lbf. hinge hang/stress test
- ▶ Warranty: 1-year limited

APPLICATIONS

- ▶ Engine Block Heaters
- ▶ Receptacle Protection
- ▶ Walk-in Refrigeration Cooler/Freezer

TECHNICAL DATA

General

Model Number	WP3110MXD
Description	Extra-Duty Die-Cast In-Use Weatherproof Cover, Single-Gang, Vrt, 2.75" Gray
UPC Code	078275130098
Brand	Intermatic
Country of Origin (Intermatic)	CHINA
Warranty Period	1-Year limited

Mechanical Specifications

Number of Included Inserts	3
Insert Types Included	WP17
Hinge Direction	Vertical
Is Extra-Duty Rated	Yes

Dimensions

Product Dimensions (H x W x D) in	6 3/8 x 3 4/5 x 2 3/4 in
Accepted Cord Size Max	1x12 AWG
Box Type	Single

Material Specifications

Color	Gray
-------	------

Packaging

Shipping Weight (lbs)	0.9
Unit Carton Dimensions (H x W x L) in	2.875 x 3.875 x 6.375 in

Standards and Certifications

UL Certification	cULus
CSA Certification	cCSAus
Other Certifications and Compatibilities	REACH
California Proposition 65	None

ACCESSORIES



WP17
Single-Gang Inserts (3)