

Weather Proof Cover - Low-Profile Extra-Duty Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hrz, Clear, 3/0 Adapter Plate

Item WP7003G



PRODUCT DESCRIPTION

Plastic In-Use Weatherproof Covers are easy to install and include a gasket, mounting screws, base, cover assembly and inserts to meet the needs of a variety of applications.

FEATURES

- ▶ Includes 3/0 adapter plate for 3" (76 mm) round box
- ▶ 100% Paintable surface
- ▶ Complies with 2020 NEC Article 406.9 (B)(1) for wet locations and extra-duty applications
- ▶ Exceeds CEC Section 26-702
- ▶ UL Certified for Type 3R outdoor enclosures
- ▶ Meets requirements for cold impact testing: -60° F (-51° C)
- ▶ Heavy-duty UV stabilized polycarbonate cover, mounting base, and inserts
- ▶ 1/8" (3 mm) thick, neoprene gasket with slits for mounting screws
- ▶ Lockable hasp: All models accept up to 0.19" dia shank
- ▶ Impact rated: 12 lbf. impact test to ensure cover remains intact

APPLICATIONS

- ▶ Receptacle Protection

TECHNICAL DATA

General	
Model Number	WP7003G
Description	Low-Profile Extra-Duty Plastic In-Use Weatherproof Cover, Single-Gang, Vrt/Hrz, Clear, 3/0 Adapter Plate
UPC Code	078275150539
Brand	Intermatic
Country of Origin (Intermatic)	MEXICO
Warranty Period	1-Year limited
Mechanical Specifications	
Number of Included Inserts	2
Hinge Direction	Vertical/Horizontal
Is Extra-Duty Rated	Yes
Dimensions	
Product Dimensions (H x W x D) in	5.5 x 3.75 x 1.5 in
Expandable Depth Mm	54
Expandable Depth In	2.125
Accepted Cord Size Max	1x16 AWG
Box Type	Single
Material Specifications	
Color	Clear; Gray
Weatherproof Cover Material	UV Stabilized Plastic

Packaging

Shipping Weight (lbs)	0.5
Unit Carton Dimensions (H x W x L) in	1.675 x 4 x 5.5 in

Standards and Certifications

UL Certification	cULus
CSA Certification	cCSAus
California Proposition 65	None
RoHS Certification	Yes