

SELF-DUMPING HOPPERS

DH SERIES

The **Self-Dumping Forklift Hopper** is designed for various material handling jobs including construction, waste management, sanitation and more.



DH-05BR-LD



Model	Weight	Length	Width	Height	Caster Type	Volume	Uniform Capacity*
LIGHT DUTY:							
DH-05BR-LD	348 lbs.	54"	34"	39"	None	1/2 cu. yd	2,000 lbs.
DH-05BRMR8-2R2SLD	390 lbs.	54"	34"	49"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	1/2 cu. yd	2,000 lbs.
DH-10BR-LD	392 lbs.	61"	46"	43"	None	1 cu. yd	2,000 lbs.
DH-10BRMR8-2R2SLD	430 lbs.	61"	46"	53"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	1 cu. yd	2,000 lbs.
DH-20BR-LD	542 lbs.	66.5"	57"	43"	None	2 cu. yd	2,000 lbs.
DH-20BRMR8-2R2SLD	584 lbs.	66.5"	57"	53"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	2 cu. yd	2,000 lbs.
DH-30BR-LD	620 lbs.	69"	81"	52"	None	3 cu. yd	2,000 lbs.
DH-30BRMR8-2R2SLD	662 lbs.	69"	81"	62"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	3 cu. yd	2,000 lbs.
MEDIUM DUTY:							
DH-05BR-MD	358 lbs.	54"	34"	39"	None	1/2 cu. yd	4,000 lbs.
DH-05BRMR8-2R2SMD	400 lbs.	54"	34"	49"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	1/2 cu. yd	3,000 lbs.
DH-10BR-MD	430 lbs.	61"	46"	43"	None	1 cu. yd	4,000 lbs.
DH-10BRMR8-2R2SMD	468 lbs.	61"	46"	53"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	1 cu. yd	3,000 lbs.
DH-20BR-MD	611 lbs.	66.5"	57"	43"	None	2 cu. yd	4,000 lbs.
DH-20BRMR8-2R2SMD	653 lbs.	66.5"	57"	53"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	2 cu. yd	3,000 lbs.
DH-30BR-MD	738 lbs.	69"	81"	52"	None	3 cu. yd	4,000 lbs.
DH-30BRMR8-2R2SMD	780 lbs.	69"	81"	62"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	3 cu. yd	3,000 lbs.

DHM SERIES

The **DHM Series Self-Dumping Mobile Hopper** makes handling commercial or industrial waste or bulk material easy and efficient. This hopper features casters and useable forklift pockets for easy mobility for collection of debris and forklift dumping to empty contents.

DHM-15PH8-2R2S



Model	Weight	Length	Width	Height	Caster Type	Volume	Uniform Capacity*
DHM-10PH8-2R2S	330 lbs.	55"	55.5"	38"	8" Phenolic casters: 2 Rigid, 2 Swivel	1 cu. yd.	2,000 lbs.
DHM-10MR8-2R2S	330 lbs.	55"	55.5"	38"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	1 cu. yd.	2,000 lbs.
DHM-15PH8-2R2S	355 lbs.	55.75"	56"	50.5"	8" Phenolic casters: 2 Rigid, 2 Swivel	1.5 cu. yds.	2,000 lbs.
DHM-15MR8-2R2S	355 lbs.	55.75"	56"	50.5"	8" Mold-on-rubber casters: 2 Rigid, 2 Swivel	1.5 cu. yds.	2,000 lbs.

*NOTE: Always distribute load evenly. When uniform weight capacity is calculated for any product, the capacity is based on the weight being uniformly distributed over the entire usable area. For those products with casters or wheels, the maximum weight capacity is the lowest weight capacity of either the product or the set of casters/wheels.