

Steel Drum Funnel for Flammables, 32" Flame Arrester, Self-Closing Cover, 2" Bung, Red - 08205

Product Images



Short Description

- Large steel funnel with self-closing cover and 32-inch flame arrester
- For use with flammables.

Description

Funnels intended for use with flammables are fitted with a brass flame arrester that absorbs and dissipates heat, preventing any external ignition source (like sparks from power tools, static electricity or cigarettes) from reaching the drum's flammable contents. Heavy 18-gauge galvanized steel, with electrostatically applied epoxy powder-coat finish, provides durability and chemical resistance. Self-close models have a fusible link that melts at 165°F (74°C) shutting the cover automatically in case of a fire to extinguish the flames.

Popular funnel No. 08207 with 6" (152mm) flame arrester handles most needs, while No. 08205 with 32" (813mm) flame arrester provides greater liquid flow. For viscous flammable or nonflammable liquids, funnel No. 08208 is fitted with a 33" (838mm) open-end brass tube to direct liquid flow. All funnels comply with EPA and OSHA regulations and are FM approved. Larger funnels accept a lock to prevent unauthorized access.

Note: It is important to segregate incompatible wastes to avoid chemical reactions or explosions. Store drums properly indoors, or in a weather-protected area outside. Funnels can be left in place on the drums.

Specifications

Model No	08205
UPC	697841001206
International Model No.	08205
Pallet Quantity	9
Material Specifications	Galvanized Steel
FM Approval	Yes
TUV Approval	Yes
Flame Arrestor, inch	32
Flame Arrestor, mm	813
Flame Arrestor Material	Brass
Cover Type / Closure Type	Self Close
NPS/NPT inch	2
NPS/NPT mm	51
Funnel Dimensions	10.75" Dia x 10" H
	273mm Dia x 254mm H
Funnel Capacity - gallon	2.6
Funnel Capacity - liter	10
Mouth Diameter - inch	10.75
Mouth Diameter - mm	273
Net Weight, lbs	12.0
Net Weight, kg	5.4