

2 Gallon Steel Bench Can, with Perforated Dasher Plate, Yellow - 10578

Product Images



Short Description

- Easily clean small parts in solvent
- Spring loaded, perforated dasher plate
- Hinged cover minimizes evaporation losses

Description

Simply place work on spring-loaded, perforated dasher plate, press down and agitate, then release to return dasher to drain position. Plated steel dasher also works as an effective flame arrester to reduce the risk of fire flashback. Hinged cover minimizes evaporation losses and protected rim reduces the possibility of hand injury. Cans are made of sturdy 24-gauge steel with tough powder-coat finish.

Specifications

Model No	10578
UPC	697841041349
International Model No.	10578
FM Approval	Yes
TUV Approval	Yes
Color	Yellow
Material Specifications	Steel
Dimensions, Exterior	5.875" H x 11.5" Outer Dia.
	149mm H x 292mm Outer Dia.
Capacity	2 gallon
Liter Capacity	8
Dasher (Inch)	9.75
Dasher, mm	248
Net Weight, lbs	6.3
Net Weight, kg	2.9