

5 Gallon Poly Disposal Safety Can, Flame Arrester, White - 12754

Product Images



Short Description

- Superior chemical resistance and leak protection
- Spring-loaded sealed cap automatically vents
- Stainless steel flame arrester
- Design resists accidental tip over

Description

High-density polyethylene (HDPE) disposal cans provide superior chemical resistance and leak protection. Spring-loaded sealed cap, normally closed, automatically vents between 3 and 5 psi (0.2 and 0.35 bar). Stainless steel handle and hardware with latch-catch system hold the cap in the open position for easy filling and pouring. Large-mouth opening features a built-in stainless steel flame arrester to guard against outside ignition. A current-carrying, patented carbon insert embedded in the container allows for proper grounding. The broad-base design provides stability and resists accidental tip over.

Specifications

Model No	12754
UPC	697841056985
International Model No.	12754
Pallet Quantity	24
FM Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Color	white
Material Specifications	Polyethylene
Dimensions, Exterior	20" H x 12" Outer Dia. 508mm H x 305mm Outer Dia.
Capacity	5 gallon
Liter Capacity	19
Fill/Pour Hole inch	3.65
Fill/Pour Hole mm	93
Net Weight, lbs	8.0
Net Weight, kg	3.6