

53mm Carboy Cap, Open Top with Adapter, Two 5/16" Molded-in Hose Barbs and Vent - 12856

Product Images



Short Description

- Quick-connect cap adapters for quick and easy port changes
- Two-piece open cap and adapter design prevents tube twisting when opening
- Polypropylene (PP) caps and adapters are autoclavable

Description

- Quick-connect cap adapters for quick and easy port changes
- Two-piece open cap and adapter design prevents tube twisting when opening
- Polypropylene (PP) caps and adapters are autoclavable

Leakproof, PP caps and interchangeable cap adapters provide a wide range of top connection configurations. Each cap is compatible with several adapters allowing you to change and configure carboy top connections based on your application requirements. Designed to be stackable, the caps feature large grips allowing you to easily open and tighten, and include platinum-cured silicone gaskets. Adapters are available with quick connect hose barb options including two, three, or four port combinations, as well as molded-in hose barb options, offering additional top connection flexibility.

Recommended autoclave cycle: 15 PSI and 250 ° F (121 ° C) for 20 minutes.

Specifications

Model No	12856
UPC	697841181045
International Model No.	12856
Material Specifications	Polypropylene
Dimensions, Exterior	3.6" H x 3" Outer Dia. 91mm H x 76mm Outer Dia.
Net Weight, lbs	0.2
Net Weight, kg	0.1