

120mm Adapter for Carboy Cap, Closed -12877

Product Images



Short Description

- Quick-connect cap adapters for quick and easy port changes
- Two-piece open cap and adapter design prevents tube twisting when opening
- Polypropylene (PP) caps and adapters are autoclavable

Description

Leakproof, PP caps and interchangeable cap adapters provide a wide range of top connection configurations. Each cap is compatible with several adapters allowing you to change and configure carboy top connections based on your application requirements. Designed to be stackable, the caps feature large grips allowing you to easily open and tighten, and include platinum-cured silicone gaskets. Adapters are available with quick connect hose barb options including two, three, or four port combinations, as well as molded-in hose barb options, offering additional top connection flexibility.

Recommended autoclave cycle: 15 PSI and 250 ° F (121 ° C) for 20 minutes.

Specifications

Model No	12877
UPC	697841182301
International Model No.	12877
Material Specifications	Polypropylene
Dimensions, Exterior	2.1" H x 4.7" Outer Dia.
	53mm H x 119mm Outer Dia.
Cap Size	120mm
Net Weight, lbs	0.7
Net Weight, kg	0.3