

20 Liter HDPE Carboy, 83mm Cap - 12910

Product Images



Short Description

- Excellent chemical compatibility for storing and dispensing solvents, buffers, reagents and powders
- Interchangeable caps and adapters provide top connection flexibility
- Rectangular ergonomic design saves valuable bench space
- Material, volume, and metric graduation marks imprinted on carboys
- Constructed from USP Class VI, FDA grade materials

Description

- Interchangeable caps and adapters provide top connection flexibility
- Rectangular ergonomic design saves valuable bench space
- Material, volume, and metric graduation marks imprinted on carboys
- Constructed from USP Class VI, FDA grade materials

Made of highly durable Class VI, FDA grade high-density polyethylene resin, these carboys offer excellent chemical resistance and are ideal for various solvents, buffers, reagents, powders, and solids. The ergonomic design features large handles and base with molded hand-grip, allowing you to easily lift and pour. Available in 83-mm and 120-mm sizes, the included polypropylene cap with platinum-cured silicone gasket provides a tight spill-proof seal. The larger 120-mm neck size allows you to reach into the carboy for quick and easy cleaning.

Carboys are compatible with interchangeable caps and adapters. Select from a wide range of adapters with molded or quick connect hose barb configurations for top connection flexibility.

Specifications

Model No	12910
UPC	697841181267
International Model No.	12910
Material Specifications	High Density Polyethylene
Dimensions, Exterior	24.2" H x 8.1" W x 13.6" L
	615mm H x 206mm W x 345mm L
Capacity	5.3 gallon
Liter Capacity	20
Cap Size	83mm
Net Weight, lbs	5.0
Net Weight, kg	2.3