

20 Liter HDPE Carboy With Spigot, 83mm Cap - 12916

Product Images



Short Description

- Interchangeable caps and adapters provide top connection flexibility
- Rectangular ergonomic design saves valuable bench space
- Material, volume, and metric graduation marks imprinted on carboys
- Constructed from USP Class VI, FDA grade materials

- Leakproof spigot includes easy-grip lever controlling two flow rates

Description

Made of highly durable Class VI, FDA grade high-density polyethylene resin, these carboys offer excellent chemical resistance and are ideal for various solvents, buffers, reagents, powders, and solids. The ergonomic design features large handles and base with molded hand-grip, allowing you to easily lift and pour. Available in 83-mm and 120-mm sizes, the included polypropylene cap with platinum-cured silicone gasket provides a tight spill-proof seal. The larger 120-mm neck size allows you to reach into the carboy for quick and easy cleaning.

Designed with internal threads and a hard stop to prevent over tightening and seal damage, leakproof polypropylene spigots feature 5/8- and 3/4-inch hose barbs, and a standard internal luer taper to fit a male barb adapter. Large lever controls two flow rates, one for continuous, locked flow and the other for a faster, manual flow. Carboys are compatible with interchangeable adapters and spigot fittings. Select from a wide range of adapters with molded or quick connect hose barb configurations for top connection flexibility, and additional spigots and versatile barbs for alternate bottom hosing connection options

Note: Length includes spigot.

Specifications

Model No	12916
UPC	697841181328
International Model No.	12916
Material Specifications	High Density Polyethylene
Dimensions, Exterior	24.2" H x 8.1" W x 15.25" L
	615mm H x 206mm W x 387mm L
Capacity	5.3 gallon
Liter Capacity	20
Cap Size	83mm
Net Weight, lbs	5.0
Net Weight, kg	2.3